



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



QC3030H Type QC BRKR 3P 30A 240VAC Max 10kaic *Eaton Corp*

| | |
|------------------|--|
| Catalog Number | QC3030H |
| Manufacturer | Eaton Corp |
| Description | Thermal Magnetic Circuit Breaker, 30 A, Non-Interchangeable Tripping Mechanism, Cable-In/Cable-Out Terminal, Panel Mount, 240 V Ac, 4.9 In Overall Height, 3.8 In Overall Length |
| Weight per unit | 1.1 (lbs/each) |
| Product Category | 3 Pole Din Rail Mount Circuit |

Features

| | |
|------------|-----------------------------------|
| dimensions | 3.8000 IN X 3.2000 IN X 4.9000 IN |
| Poles | 3 |

Descriptions

| | |
|------------------------|---|
| Description | TYPE QC BRKR 3P 30A 240VAC MAX 10KAIC |
| extra long description | ETN QC3030H TYPE QC BREAKER 3P 30A |
| Features | Eaton has a wide selection of UL rated miniature circuit breakers for loadcenters, fuseboxes, or similar devices. Each pole provides steel frame calibration and arc chutes with 5 - 100A continuous in one-, two-, and three-pole designs. A full-range of accessories expand customization options, including various mounting and ring tung termination options. |

Manufacturer Information

| | |
|------|----------------|
| GTIN | 00786679240106 |
| UPC | 786679240106 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------------|
| Category Description | MOLDED CASE BREAKERS |
| Type | Thermal magnetic circuit breakers |

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Package | 8 |
| Weight Per each | 1.1 |

Uses, Certifications, and Standards

| | |
|-------------|--|
| Application | Datacenters - IT Space: CI and Hyper ConvergedOtherMarine Vessels and Equipment - Marine Vessels and Equipment - OtherGeneration - Conventional Energy - Conventional EnergyGeneration - Renewable Energy - Alternative Energy |
| standard | UL Listed,CSA Certified |