



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TMCX4140 1-1/4" Cord Grips *Crouse-Hinds*

| | |
|------------------|---|
| Catalog Number | TMCX4140 |
| Manufacturer | Crouse-Hinds |
| Description | TMC Armored Cable Gland, Aluminum, 1-1/4 In Size, 3.125 In (Gland) Length, -25 °C Operating Temperature, +60 °C Operating Temperature, Grip Connection, Non-Insulated, 1.08 LB/Ea |
| Weight per unit | 1.1 (lbs/each) |
| Product Category | BX, MC, Armored Cable Fittings |

Features

| | |
|------------|-----------------------------------|
| connection | Male NPT |
| dimensions | 4.1000 IN X 2.4400 IN X 2.4400 IN |

Material, Color, and Finish

| | |
|--------|---------------|
| Finish | Nickel Plated |
|--------|---------------|

Descriptions

| | |
|------------------------|--|
| Description | 1-1/4" CORD GRIPS |
| extra long description | CRS-H TMCX4140 1 1/4 FT MC CAB ARMO |
| Features | For use with metal-clad, non-armoured and tray cable, TMCX cable fittings are installed to provide a means for terminating cable at junction boxes, control centers, panelboards and enclosures for motor control and electrical distribution. They are used to form a mechanical watertight connection and to provide ground continuity of cable armour. Applied in Division 1 locations and when a seal is required. |

Manufacturer Information

| | |
|-------|---------------------------|
| Brand | EATON CROUSE-HINDS SERIES |
| GTIN | 00782274414690 |
| UPC | 782274414690 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------------------|
| Category Description | CORD CONNECTORS & CORD GRIPS |
| Type | Cable gland |

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Weight Per each | 1.075 |

Uses, Certifications, and Standards

| | |
|--------------------|--|
| Enclosure standard | IP56, Class I Div 1 Group A B C D, Class II, Class III |
| Temperature Rating | UL (CANADA AND US), CUL -25 To 60 Deg C |