

Specifications



Photo is representative



Eaton S811+T24N3S

Eaton S811+ soft starter, 240 A, T-frame, Three pole, 24 V power, 200-600 V operating voltage, 47-63 Hz, 1-2 conductors, #4 AWG to 500 kcmil wire, 120 Vdc, 240 Vac, Modbus RTU, NEMA 0, LCD display, -30°C to -50°C

General specifications

PRODUCT NAME	Eaton S811+ soft starter
CATALOG NUMBER	S811+T24N3S
UPC	786685558981
PRODUCT LENGTH/DEPTH	6.47 in
PRODUCT HEIGHT	12.71 in
PRODUCT WIDTH	7.65 in
PRODUCT WEIGHT	45 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	CE Marked
CERTIFICATIONS	UL Recognized CSA file No. 3211-06 UL Listed IEC 60947-4-2 EN 60947-4-2 CSA Certified for Elevator Duty
CATALOG NOTES	All units require a 24 Vdc power supply found on catalog Page V6-T1-85, or equivalent., S811+T_, S811+U_ and S811+V_ units require lug kits, S811+U50_ unit does not have IEC certification.

Product specifications

USED WITH	Three-phase motors
AMPERAGE RATING	240A
DISPLAY MATERIAL	LCD
AC CURRENT - MAX	240 Vac
DC CURRENT - MAX	120 Vdc
NUMBER OF POLES	Three-pole
TYPE	Soft starter
FREQUENCY RATING	47-63 Hz
POWER SUPPLY	24 V
FRAME SIZE	T
OPERATING TEMPERATURE - MAX	50 °C
COMMUNICATION	Modbus RTU
NEMA RATING	NEMA 0
SIZE	NEMA 0
OPERATING VOLTAGE	200-600 V
WIRE SIZE	#4 AWG-500 kcmil
MODULE INTERFACE	Digital interface module
OPERATING TEMPERATURE - MIN	-30 °C

Resources

CATALOGS	Product Range Catalog Drives Engineering
	Soft starter DS7 up to 200 A
MULTIMEDIA	Soft Starter Product Family Overview
	Soft Starter DS7 up to 32 A
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - S811+T24N3S

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications



Photo is representative



Eaton S811+T24N3S

Eaton S811+ soft starter, 240 A, T-frame, Three pole, 24 V power, 200-600 V operating voltage, 47-63 Hz, 1-2 conductors, #4 AWG to 500 kcmil wire, 120 Vdc, 240 Vac, Modbus RTU, NEMA 0, LCD display, -30°C to -50°C

General specifications

PRODUCT NAME	Eaton S811+ soft starter
CATALOG NUMBER	S811+T24N3S
UPC	786685558981
PRODUCT LENGTH/DEPTH	6.47 in
PRODUCT HEIGHT	12.71 in
PRODUCT WIDTH	7.65 in
PRODUCT WEIGHT	45 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	CE Marked
CERTIFICATIONS	UL Recognized CSA file No. 3211-06 UL Listed IEC 60947-4-2 EN 60947-4-2 CSA Certified for Elevator Duty
CATALOG NOTES	All units require a 24 Vdc power supply found on catalog Page V6-T1-85, or equivalent., S811+T_, S811+U_ and S811+V_ units require lug kits, S811+U50_ unit does not have IEC certification.

Product specifications

USED WITH	Three-phase motors
AMPERAGE RATING	240A
DISPLAY MATERIAL	LCD
AC CURRENT - MAX	240 Vac
DC CURRENT - MAX	120 Vdc
NUMBER OF POLES	Three-pole
TYPE	Soft starter
FREQUENCY RATING	47-63 Hz
POWER SUPPLY	24 V
FRAME SIZE	T
OPERATING TEMPERATURE - MAX	50 °C
COMMUNICATION	Modbus RTU
NEMA RATING	NEMA 0
SIZE	NEMA 0
OPERATING VOLTAGE	200-600 V
WIRE SIZE	#4 AWG-500 kcmil
MODULE INTERFACE	Digital interface module
OPERATING TEMPERATURE - MIN	-30 °C

Resources

CATALOGS	Product Range Catalog Drives Engineering
	Soft starter DS7 up to 200 A
MULTIMEDIA	Soft Starter Product Family Overview
	Soft Starter DS7 up to 32 A
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - S811+T24N3S

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

