



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TY524M 5.50" "Ty-Rap" Cable Tie

Abb Installation Products, Inc

Catalog Number	TY524M
Manufacturer	Abb Installation Products, Inc
Description	Cable Tie, Natural Polyamide (Nylon 6.6) For Temperatures Up to 85 Degrees Celsius (185 F) For Indoor Applications, UI/En/CSA62275 Type 2/21 Rated For Ah-2 Plenum, Length Of 137MM (5.4 Inches), Width Of 3.6MM (0.142 Inches) (0.14 Inches), Thickness Of 1MM (0.04 Inch), Tensile Strength Rating Of 178 Newtons (40 Pounds)
Weight per unit	0.0010 (lbs/each)
Product Category	Cable Ties & Wraps

Features

Tensile Strength	40:178
------------------	--------

Dimensions and Weight

Length	5.4
Thickness	0.04
Width	0.14

Descriptions

Description	5.50" "TY-RAP" CABLE TIE
extra long description	ABB TY524M CABLE TIE 40LB 5.5IN NAT
Long Description	Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum, Length of 137mm (5.4 Inches), Width of 3.6mm (0.142 Inches) (0.14 Inches), Thickness of 1mm (0.04 Inch), Tensile Strength Rating of 178 Newtons (40 Pounds)
Product Type	Cable Tie 40LB 5.5IN Nat Nylon 2-PC
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time

Manufacturer Information

Brand	Ty-Rap
GTIN	00786210806051
Manufacturers Part Number	TY524M
UPC	786210806051

Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	HIGH PERFORMANCE



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	100
Package	1000
Weight Per each	0.001

Uses, Certifications, and Standards

standard	UL E49405
----------	-----------