





Low Voltage Brackets

Steel

- Eliminates the need for an electrical box when installing low voltage Class 2 wiring
- For old work or new work
- Installs easily with a drywall saw and screwdriver

			
CIMB-0	CIMB-1	CICSB-1	WBF-1

Cat. No.	Description
Low Voltage Mounting Brackets	
CIMB-0	Flat mounting brackets that provides quick installation of low voltage class 2 communication outlets Positioning tabs ensure straight installation
CIMB-1	Mounting bracket that provides quick installation of low voltage class 2 communication outlets. Raised 1/2 in. Positioning tabs ensure straight installation
CICSB-1	Mounting brackets that provides quick installation of low voltage communication outlets May be used with all 2-1/2 in. deep gangable boxes
WBF-1	Low voltage wall bracket


			
CI1544	CI1544P	CIS-1X2	CIS-1 / CIS-4




Cat. No.	Dimensions (in.)		Hole Size (in.)	Suggested Application
	H	W		NMD90 (loomex)
Nailing Straps (Zinc Plated Steel)				
CI1544	0.25	0.51	-	14/2-12/2
Nailing Straps (Polyethylene)				
CI1544-P	0.25	0.49	-	14/2-12/2
CI1546-P	0.25	0.75		14/2-8/2
Cable Staples (Galvanized Steel)				
CIS-1	0.25	0.48	-	14/2-12/2
CIS-2	0.44	0.54		2 cables 14/2; 2 cables 12/2 14/2-14/3-12/2-12/3-10/2-10/3
CIS-3	0.49	0.70		10/2-8/2; 14/3-10/3
CIS-4	0.76	0.86		8/3-6/3
Double Cable Staples (Galvanized Steel)				
CI1S-1X2	0.25	0.48 x 2	-	14/2-12/2
CI1S-1X2-FP3				
CI1S-1X2-FP5				



Low Voltage Brackets

Nonmetallic

		
SC100A	SC200A	SC300A
Open-backed to easily accommodate the bend radiuses required for low voltage cabling and deep devices such as volume controls, and is designed to fit a standard two-gang three-gang faceplate. It also features an easy nail-on mounting or screw-in bracket, while more hard shell provides increased durability and no racking.		

			
SC100RR	SC200RR	SC100SC	SC100ADJC
Swing arm rework bracket. 1 gang.	Swing arm rework bracket. 2 gang.	This low voltage bracket provides a low voltage outlet next to a previously installed high voltage outlet. For new construction and rework. Attaches easily to most electrical boxes, and is designed to fit a standard two-gang faceplate.	New work adjustable low voltage bracket. 1 gang.







Cat. No.	Description
Low Voltage Brackets	
SC100A	One-Gang backless bracket 2.32 in. W x 3.73 in. L
SC200A	Two-Gang backless bracket 5.35 in. W x 3.81 in. L
SC300A	Three-Gang backless bracket 8.69 in. W x 7.20 in. L
Old Work Backless Brackets	
SC100RR	One-Gang backless old work bracket w/ swing clamps 2-1/4 in. x 3-1/4 in.
SC200RR	Two-Gang backless old work bracket w/ swing clamps 3.92 in. x 4.00 in.
Low Voltage Add-On Bracket	
SC100SC	One-Gang Add-On Bracket 1.80 in. W x 3.68 in. L
One-Gang and Two Gang – Low Voltage	
SC100ADJC	One-Gang adjustable bracketless bracket 3-7/8 in. W x 3-3/4 in. H
SC200ADJC	Two-Gang adjustable bracketless bracket 5-5/8 in. W x 3-5/8 in. H

CSA not applicable

Low Voltage Brackets

Steel

- Eliminates the need for an electrical box when installing low voltage Class 2 wiring
- For old work or new work
- Installs easily with a drywall saw and screwdriver

			
CIMB-0	CIMB-1	CICSB-1	WBF-1

Cat. No.	Description
Low Voltage Mounting Brackets	
CIMB-0	Flat mounting brackets that provides quick installation of low voltage class 2 communication outlets Positioning tabs ensure straight installation
CIMB-1	Mounting bracket that provides quick installation of low voltage class 2 communication outlets. Raised 1/2 in. Positioning tabs ensure straight installation
CICSB-1	Mounting brackets that provides quick installation of low voltage communication outlets May be used with all 2-1/2 in. deep gangable boxes
WBF-1	Low voltage wall bracket

			
CI1544	CI1544P	CIS-1X2	CIS-1 / CIS-4


Cat. No.	Dimensions (in.)		Hole Size (in.)	Suggested Application
	H	W		NMD90 (loomex)
Nailing Straps (Zinc Plated Steel)				
CI1544	0.25	0.51	-	14/2-12/2
Nailing Straps (Polyethylene)				
CI1544-P	0.25	0.49	-	14/2-12/2
CI1546-P	0.25	0.75		14/2-8/2
Cable Staples (Galvanized Steel)				
CIS-1	0.25	0.48	-	14/2-12/2
CIS-2	0.44	0.54		2 cables 14/2; 2 cables 12/2 14/2-14/3-12/2-12/3-10/2-10/3
CIS-3	0.49	0.70		10/2-8/2; 14/3-10/3
CIS-4	0.76	0.86		8/3-6/3
Double Cable Staples (Galvanized Steel)				
CI1544-1X2	0.25	0.48 x 2	-	14/2-12/2
CI1544-1X2-FP3				
CI1544-1X2-FP5				



Low Voltage Brackets

Nonmetallic


SC100A

SC200A

SC300A

Open-backed to easily accommodate the bend radiuses required for low voltage cabling and deep devices such as volume controls, and is designed to fit a standard two-gang three-gang faceplate. It also features an easy nail-on mounting or screw-in bracket, while more hard shell provides increased durability and no racking.


SC100RR

Swing arm rework bracket. 1 gang.


SC200RR

Swing arm rework bracket. 2 gang.


SC100SC

This low voltage bracket provides a low voltage outlet next to a previously installed high voltage outlet. For new construction and rework. Attaches easily to most electrical boxes, and is designed to fit a standard two-gang faceplate.


SC100ADJC

New work adjustable low voltage bracket. 1 gang.



Cat. No.	Description
Low Voltage Brackets	
SC100A	One-Gang backless bracket 2.32 in. W x 3.73 in. L
SC200A	Two-Gang backless bracket 5.35 in. W x 3.81 in. L
SC300A	Three-Gang backless bracket 8.69 in. W x 7.20 in. L
Old Work Backless Brackets	
SC100RR	One-Gang backless old work bracket w/ swing clamps 2-1/4 in. x 3-1/4 in.
SC200RR	Two-Gang backless old work bracket w/ swing clamps 3.92 in. x 4.00 in.
Low Voltage Add-On Bracket	
SC100SC	One-Gang Add-On Bracket 1.80 in. W x 3.68 in. L
One-Gang and Two Gang – Low Voltage	
SC100ADJC	One-Gang adjustable bracketless bracket 3-7/8 in. W x 3-3/4 in. H
SC200ADJC	Two-Gang adjustable bracketless bracket 5-5/8 in. W x 3-5/8 in. H

CSA not applicable