

## ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941 Fax: 936-560-4685



## **SC850S10C 7.87" 50LB Nat CBL Tie** *Panduit Corporation*

Catalog Number	SC850S10C
Manufacturer	Panduit Corporation
Description	The SC8-50-S10-C Stronghold Clamp Cable Ties Offers
	Contractors An Economical Clamp Cable Tie Option For
	Commercial Construction and General-Purpose Applications. The
	Cable Tie Design Allows You to Secure Cable Bundles to Another
	Surface, For Use With #10 (M5) Screw. Standard, 7.87" (200MM)
	Length, Made Of Nylon 6.6, Are Natural In Color and Come In Packages Of 100.
Weight per unit	0.3670 (lbs/each)
Product Category	Cable Ties & Wraps
Features	
media	Yes
Tensile Strength	50
<b>Dimensions and Weight</b>	
Length	7.9
Thickness	0.06
Width	NA
Descriptions	
Description	7.87" 50LB NAT CBL TIE
extra long description	PAN SC8-50-S10-C StrongHold™ SC8-50
Long Description	The SC8-50-S10-C StrongHold Clamp Cable Ties offers contractors an economical clamp cable tie option for commercial construction and general-purpose applications. The cable tie design allows you to secure cable bundles to another surface, for use with #10 (M5) screw. Standard, 7.87" (200mm) length, made of Nylon 6.6, are natural in color and come in packages of 100.
Product Type	Stronghold™ SC8-50-S10-C Cable Tie, Nat., Pa 6.6, 50LB Min L
Special Features	Indoor
Manufacturer Information	
Brand	Panduit®
GTIN	00613056258327
Manufacturers Part Number	SC8-50-S10-C
UPC	613056258327

## **Taxonomies, Classifications, and Categories**

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Туре	Cable Tie



## ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941 Fax: 936-560-4685

Availability minimum qty	100
Packaging	
Carton	100
Package	1000
Weight Per each	0.367
Uses, Certifications, and Standards	
standard	UL 62275 Compliant (Type 1, 11), UL Recognized #E56854, RoHS Compliant