



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SKABO Easy Splice Alcu Butt Splice 1/0 Awg *Nsi Industries*

Catalog Number	SKAB0
Manufacturer	Nsi Industries
Description	Easy-Splice Dual Rated Direct Burial Butt Splice Kit For #6 to 1/0 Awg Utilizing A Mechanical Dual Rated Splice and Matched Heavy Wall Heat Shrink Tubing to Create An Insulated Splice For Copper and/or Aluminum Cables. Temperature Rating 105 Degrees C. 600 Volt Maximum.
Weight per unit	0.1680 (lbs/each)
Product Category	Splicing & Terminating Kits

Features

Cable Size	6-1/0 AWG
Cable Type	Class A-B
insulation	Heat Shrink
Voltage Rating	600 V
Warranty	1 YEAR

Material, Color, and Finish

Color	Black
-------	-------

Descriptions

Description	EASY SPLICE ALCU BUTT SPLICE 1/0 AWG
extra long description	NSI SKAB-0 Easy Splice ALCU Butt Sp
Features	Easy-Splice Dual Rated Direct Burial Butt Splice Kit for #6 to 1/0 AWG Utilizing a mechanical dual rated splice and matched heavy wall heat shrink tubing to create an insulated splice for copper and/or aluminum cables. Temperature Rating 105 degrees C. 600 Volt Maximum.
Long Description	Easy-Splice Dual Rated Direct Burial Butt Splice Kit for #6 to 1/0 AWG Utilizing a mechanical dual rated splice and matched heavy wall heat shrink tubing to create an insulated splice for copper and/or aluminum cables. Temperature Rating 105 degrees C. 600 Volt Maximum.
Product Type	Easy Splice Alcu Butt Splice 1/0
Special Features	Dual Rated For Use With Copper And Aluminum Cable

Manufacturer Information

Brand	Nsi Industries
GTIN	00662381169136
Manufacturers Part Number	SKAB-0
UPC	662381169136



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Type Direct Burial Splice Kit With Heat Shrink

Packaging

Carton 1

Weight Per each 0.168

Uses, Certifications, and Standards

Application Splicing Wire

Operating Temperature -40 C To 90 C