



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## SP250MQMJ 250 Va Open CTRL XFRMR 240VX480V - 120X240V

*Hammond Power Solutions*

|                  |                                                                                              |
|------------------|----------------------------------------------------------------------------------------------|
| Catalog Number   | SP250MQMJ                                                                                    |
| Manufacturer     | Hammond Power Solutions                                                                      |
| Description      | General Purpose Open-Style Core & Coil Control Transformers, 240X480 PV, 120X240 SV, 250 Kva |
| Weight per unit  | 6.5 (lbs/each)                                                                               |
| Product Category | Core & Coil Industrial Control                                                               |

### Features

|         |     |
|---------|-----|
| Wattage | 250 |
|---------|-----|

### Dimensions and Weight

|        |      |
|--------|------|
| Height | 3.4  |
| Length | 3.78 |
| Width  | 4.09 |

### Descriptions

|                        |                                                                                                                          |
|------------------------|--------------------------------------------------------------------------------------------------------------------------|
| Description            | 250 VA OPEN CTRL XFRMR 240VX480V - 120X240V                                                                              |
| extra long description | HMND SP250MQMJ 250 VA 240X480 120X2                                                                                      |
| Long Description       | General Purpose Open-Style Core & Coil Control Transformers, 240x480 PV, 120x240 SV, 250 kVA                             |
| Product Type           | Spartan 240X480 PV 120X240 SV 250 Kva                                                                                    |
| Special Features       | Control transformer for stanard commercial loads without high current inrush, optional finger safe covers are available. |

### Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | HPS Spartan®   |
| GTIN                      | 00803423098780 |
| Manufacturers Part Number | SP250MQMJ      |
| UPC                       | 803423098780   |

### Taxonomies, Classifications, and Categories

|                      |                                                      |
|----------------------|------------------------------------------------------|
| Category Description | CONTROL TRANSFORMERS                                 |
| Type                 | Tranformer > Dry Type > Control > Open Core and coil |

### Packaging

|                 |     |
|-----------------|-----|
| Carton          | 1   |
| Weight Per each | 6.5 |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

|                    |                                                                                         |
|--------------------|-----------------------------------------------------------------------------------------|
| Application        | HVAC, signals and alarm systems, motor control circuits, lighting and circuit isolation |
| Enclosure          | Core and Coil                                                                           |
| Frequency Rating   | 50                                                                                      |
| Mounting           | PANEL                                                                                   |
| standard           | CSA, UL, CE                                                                             |
| Temperature Rating | Typical 30 Average/ 40 Maximum                                                          |