

# Specifications

Photo is representative

## Eaton V48M28T7516CU

Eaton General purpose ventilated transformer, Fungus proof, CU windings, DOE 2016, NEMA 2, FR942, 220°C, 75 kVA, Floor/wall mnt upright only, 3-phase, PV: 480V delta, SV: 208Y/120, NEMA ST-20, 2 at +2.5%, 4 at -2.5%, 150°C, 75 kVA

### Physical Attributes

|                          |  |
|--------------------------|--|
| <b>COIL MATERIAL</b>     | Copper   |
| <b>ENCLOSURE</b>         | NEMA   |
| <b>FRAME</b>             | FR942  |
| <b>INSULATION</b>        | 220 °C   |
| <b>MATERIAL</b>          | Copper winding                                   |
| <b>MOUNTING</b>          | Floor or wall, upright only                      |
| <b>TAP SIZE</b>          | 2 at +2.5%, 4 at -2.5%                           |
| <b>TYPE</b>              | Energy-efficient ventilated dry-type transformer |
| <b>WIRING CONNECTION</b> | 280B   |

### General specifications

|                             |  |
|-----------------------------|--|
| <b>PRODUCT NAME</b>         | Eaton General purpose ventilated transformer   |
| <b>CATALOG NUMBER</b>       | V48M28T7516CU  |
| <b>UPC</b>                  | 786680192012   |
| <b>PRODUCT LENGTH/DEPTH</b> | 24 in  |
| <b>PRODUCT HEIGHT</b>       | 43 in  |
| <b>PRODUCT WIDTH</b>        | 30.5 in  |
| <b>PRODUCT WEIGHT</b>       | 632 lb   |
| <b>WARRANTY</b>             | Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. |
| <b>COMPLIANCES</b>          | DOE2016 Efficient  |
| <b>CERTIFICATIONS</b>       | UL Listed  |
| <b>CATALOG NOTES</b>        | 10 CFR Part 431 (2016) Efficient   |

