

Eaton VMVL-7-UNV1

Catalog Number: VMVL-7-UNV1

Eaton Crouse-Hinds series Champ VMVL LED fixture, Cool white, 175W HID equivalent, No guard, Glass lens, 7000 lumens, 127 lm/W, Die cast aluminum, No mounting module, Type V, 100-277 Vac, 127-250 Vdc, 61W

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Crouse-Hinds series Champ VMVL LED light fixture	VMVL-7-UNV1
	UPC
	662276861015
Product Length/Depth	Product Height
13 in	13.13 in
Product Width	Product Weight
12.75 in	20.8 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

IEC

IECEX/ATEX

NEC hazardous rating

Class I, Division 2

Class I, Zone 2

Class II, Division 1

Class III

IECEX/ATEX hazardous rating

Zone 21

NEMA Rating

4X

Ingress protection (IP) ratings

IP66

Product specifications

Lumens

7000

Lumens per watt

127

Color temperature

Cool white

Mounting Method

No mounting module

Optical distribution

Type V

Guard type

No guard

Voltage rating

100-277 Vac, 127-250 Vdc

Frequency rating

50/60 Hz

Wattage

61W

Dimming

Dimmable driver

Power factor

> 0.90

Equivalent luminaire

175W HID

Material

Die cast aluminum

Lens material

Heat and impact resistant glass

Resources

3D models

[SP3D Design Package - Champ VMVL LED Hazardous Area Light](#)

[Fixtures](#)

Brochures

Crouse-Hinds series DLC approved lighting products

Crouse-Hinds series Global LED lighting portfolio

Crouse-Hinds series Champ VMVL LED Luminaires - 3,000 to 13,000 lumens brochure

Catalogs

Crouse-Hinds series Champ VMVL LED luminaires - 3,000 to 13,000 lumens catalog page

Installation instructions

IF 1882 - Champ VMVL and PVML LED luminaires

IF 1888 - Champ VMVL and PVML Driver Replacement

Specifications and datasheets

Eaton Specification Sheet - VMVL-7-UNV1

Champ VMV LED Hazardous Area



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton VMVL-7-UNV1

Catalog Number: VMVL-7-UNV1

Eaton Crouse-Hinds series Champ VMVL LED fixture, Cool white, 175W HID equivalent, No guard, Glass lens, 7000 lumens, 127 lm/W, Die cast aluminum, No mounting module, Type V, 100-277 Vac, 127-250 Vdc, 61W

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Crouse-Hinds series Champ VMVL LED light fixture	VMVL-7-UNV1
	UPC
	662276861015
Product Length/Depth	Product Height
13 in	13.13 in
Product Width	Product Weight
12.75 in	20.8 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

IEC

IECEX/ATEX

NEC hazardous rating

Class I, Division 2

Class I, Zone 2

Class II, Division 1

Class III

IECEX/ATEX hazardous rating

Zone 21

NEMA Rating

4X

Ingress protection (IP) ratings

IP66

Product specifications

Lumens

7000

Lumens per watt

127

Color temperature

Cool white

Mounting Method

No mounting module

Optical distribution

Type V

Guard type

No guard

Voltage rating

100-277 Vac, 127-250 Vdc

Frequency rating

50/60 Hz

Wattage

61W

Dimming

Dimmable driver

Power factor

> 0.90

Equivalent luminaire

175W HID

Material

Die cast aluminum

Lens material

Heat and impact resistant glass

Resources

3D models

[SP3D Design Package - Champ VMVL LED Hazardous Area Light](#)

[Fixtures](#)

Brochures

Crouse-Hinds series DLC approved lighting products

Crouse-Hinds series Global LED lighting portfolio

Crouse-Hinds series Champ VMVL LED Luminaires - 3,000 to 13,000 lumens brochure

Catalogs

Crouse-Hinds series Champ VMVL LED luminaires - 3,000 to 13,000 lumens catalog page

Installation instructions

IF 1882 - Champ VMVL and PVML LED luminaires

IF 1888 - Champ VMVL and PVML Driver Replacement

Specifications and datasheets

Eaton Specification Sheet - VMVL-7-UNV1

Champ VMV LED Hazardous Area



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)