



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

10101 SH 30
77845-0000, TX College Station
Phone: 979-779-6630
Fax: 979-779-6620



TB29 3/4" Alu TB MK9 Conduit Body

Crouse-Hinds

Catalog Number	TB29
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Condulet Mark 9 Conduit Outlet Body, Copper-Free Aluminum, TB Shape, 3/4"
Weight per unit	0.7100 (lbs/each)
Product Category	Alum

Features

dimensions	6.5600 IN X 1.6300 IN X 2.8800 IN
------------	-----------------------------------

Material, Color, and Finish

Finish	Untreated
--------	-----------

Dimensions and Weight

Height	2-13/32
Hub Size	3/4 in
Length	5-11/16
Width	1-9/16

Descriptions

Description	3/4" ALU TB MK9 CONDUIT BODY
extra long description	CRS-H TB29 3/4 NPT ALUMINUM TB MARK
Features	Mark 9 copper-free aluminum conduit bodies, covers and gaskets from Eaton's Crouse-Hinds Division are used in conduit systems to act as pull outlets for conductors being installed, provide openings for making splices and taps in conductors, make 90 degree bends in conduit runs, and provide for access to conductors for maintenance and future system changes. Mark 9 bodies are offered in seven different shapes, and they provide more room for heavier conductors.
Long Description	Eaton Crouse-Hinds series Condulet Mark 9 conduit outlet body, Copper-free aluminum, TB shape, 3/4"
Product Type	3/4 NPT Aluminum TB Mark 9 CNDT Body

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00782274631028
Manufacturers Part Number	TB29
UPC	782274631028

Taxonomies, Classifications, and Categories

Category Description	Form 9 condulets, covers & gaskets
Type	Conduit outlet body



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

10101 SH 30
77845-0000, TX College Station
Phone: 979-779-6630
Fax: 979-779-6620

Packaging

Carton	5
Weight Per each	0.71

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
Enclosure	Condulet
standard	UL 514B, CSA C22.2, FEDERAL SPECIFICATION W-C-586D