



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## YA1CL4BOX 1AWG 1H Lug Burndy LLC

Catalog Number	YA1CL4BOX
Manufacturer	Burndy LLC
Description	1 Awg Cu, One Hole, 3/8 Stud Size, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UI/Csa 90 Up to 35KV, Green Color Code, 11 or 375 Die Index.
Weight per unit	0.0400 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Die Index	11
Material	Copper
Voltage Rating	35

### Material, Color, and Finish

Color Code	GREEN
------------	-------

### Descriptions

Description	1AWG 1H LUG
extra long description	BUR YA1CL4BOX 1STR CU 1-HOLE SHORT
Long Description	1 AWG CU, One Hole, 3/8 Stud Size, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UL/CSA 90 Up to 35kV, GREEN Color Code, 11 or 375 Die Index.
Product Type	Terminal
Special Features	Features: UL Listed 90 DEG C, 600 V To 35 KV 45 DEG, 90 DEG Angles Are Available, Tools, Die Set Catalog Number, And (number Of Crimps): MD6, OUR840, MD7-34R Mechanical: W1CVT (1), W1CRT-1 (1), X1CRT-1 (1),BCT500HS, Y500CTHS Hydraulic: W1CVT (1),W1CRT-1 (1), X1CRT-1 (1), W29VT (4), Y35, Y39, Y750, Y46, PAT750 Hydraulic: U1CRT-1 (1), U4CABT (1), Dieless: Y1MRTC (2), MY29-3 (1), MY29-11 (1), MRC840 (1), Y644HS (1), Y81KFT (1), Y81KFTMBH (1), PAT81KFT-18V (1), Wire Strip Length: 15/16 IN, Conductor Type: Comm

### Manufacturer Information

Brand	BURNDY
GTIN	00781810551400
Manufacturers Part Number	YA1CL4BOX
UPC	781810551400

### Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Standard Barrel, Tin Plated



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	0.04

## Uses, Certifications, and Standards

Application	Wire Termination
standard	UL 486A-486B