



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



TPCATV2I 2 F Type Coax Connector In 1G TP PL I

Pass & Seymour/Legrand

| | |
|------------------|--|
| Catalog Number | TPCATV2I |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Dual 1 GHZ F-Coupler Wall Plate, Ivory (M10) |
| Weight per unit | 0.1034 (lbs/each) |
| Product Category | Outlets, Jacks, & Plates |

Features

| | |
|-----------------|----------|
| insulation | Bare |
| Number of Gangs | 1 |
| orientation | Vertical |

Dimensions and Weight

| | |
|-----------|-----|
| Size | 6" |
| Thickness | .40 |

Descriptions

| | |
|------------------------|--|
| Description | 2 F TYPE COAX CONNECTOR IN 1G TP PL I |
| extra long description | OnQ TPCATV2I 2 F TYPE COAX CONNECTO |
| Long Description | Dual 1 GHZ F-Coupler Wall Plate, Ivory (M10) |
| Product Type | 2 F Type Coax Connector In 1G TP PL I |
| Special Features | F type w/one coaxial connector, mar resistant wall plate, fits standard size single gang, nickel plate steel |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007247572 |
| Manufacturers Part Number | TPCATV2I |
| UPC | 785007247572 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------|
| Category Description | Residential plates |
| Type | Communication Device |

Availability

| | |
|--------|----------|
| Status | Inactive |
|--------|----------|

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Package | 100 |
| Weight Per each | 0.1034 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------|------------------------|
| Application | Residential/Commercial |
| Mounting | WALL |
| standard | UL 1863 |