







U2120-X



Catalog Number	U2120-X	Enclosure	G90 Galvanized Steel with Powder Coat Finish
Marketing Product Description	7 Terminal Ringless Large Closing Plate Lever Bypass Side Bussed	Jaw Quantity	7 Terminal
UPC	784572134669	Bypass Type	Lever Bypass
Length (IN)	6.5	Number of Meter Positions	1 Position
Width (IN)	17.75	Equipment Ground	Grounding Stud
Height (IN)	31.75	Hub Opening	Large Closing Plate
Brand Name	Milbank	Number Of Receptacles	0
Type	Ringless Meter Socket		
Application	Meter Socket		
Standard	UL Listed; Type 3R		
Voltage Rating	600 Volts Alternating Current		
Amperage Rating	320 Continuous Ampere		
Phase	3 Phase		
Frequency Rating	60 Hertz		
Size	6.5L x 17.75W x 31.75H		
Number Of Cutouts	0		
Cutout Size	No Main Breaker		
Cable Entry	Overhead and Underground and Side Wireway		
Terminal	3/8 Inch Stud		
Insulation	Glass Polyester		
Mounting	Surface Mount		

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.

FEATURE TABLE		
ITEM	QTY	DESCRIPTION
A	6	U/L MNTG.EMBOSS
B	1	1/4 SOLID K.O.
C	1	1/2, 3/4, 1 CONC. K.O.
D	2	2, 2 1/2, 3 CONC. K.O.
E	2	2, 2 1/2, 3, 3 1/2, 4 CONC. K.O.
F	1	3, 3 1/2, 4 CONC. K.O.



All dimensions are +/- 1/16".
Drawing views are not to scale.

Version:

1

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility, and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.







U2120-X



Catalog Number	U2120-X	Enclosure	G90 Galvanized Steel with Powder Coat Finish
Marketing Product Description	7 Terminal Ringless Large Closing Plate Lever Bypass Side Bussed	Jaw Quantity	7 Terminal
UPC	784572134669	Bypass Type	Lever Bypass
Length (IN)	6.5	Number of Meter Positions	1 Position
Width (IN)	17.75	Equipment Ground	Grounding Stud
Height (IN)	31.75	Hub Opening	Large Closing Plate
Brand Name	Milbank	Number Of Receptacles	0
Type	Ringless Meter Socket		
Application	Meter Socket		
Standard	UL Listed; Type 3R		
Voltage Rating	600 Volts Alternating Current		
Amperage Rating	320 Continuous Ampere		
Phase	3 Phase		
Frequency Rating	60 Hertz		
Size	6.5L x 17.75W x 31.75H		
Number Of Cutouts	0		
Cutout Size	No Main Breaker		
Cable Entry	Overhead and Underground and Side Wireway		
Terminal	3/8 Inch Stud		
Insulation	Glass Polyester		
Mounting	Surface Mount		

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.

FEATURE TABLE		
ITEM	QTY	DESCRIPTION
A	6	U/L MNTG.EMBOSS
B	1	1/4 SOLID K.O.
C	1	1/2, 3/4, 1 CONC. K.O.
D	2	2, 2 1/2, 3 CONC. K.O.
E	2	2, 2 1/2, 3, 3 1/2, 4 CONC. K.O.
F	1	3, 3 1/2, 4 CONC. K.O.



All dimensions are +/- 1/16".
Drawing views are not to scale.

Version:

1

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility, and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.