

Specifications

Photo is representative

Eaton V48M28T4916

Eaton General purpose ventilated transformer, Fungus proof, AL windings, DOE 2016, NEMA 2, FR943, 220°C, 150 kVA, Fl/wall mt uprt, 3-phase, PV: 480V delta, SV: 208Y/120, NEMA ST-20, 2 at +2.5%, 4 at - 2.5%, 150°C, 150 kVA, WS60, 280B

General specifications

PRODUCT NAME	Eaton General purpose ventilated transformer
CATALOG NUMBER	V48M28T4916
UPC	786680147272
PRODUCT LENGTH/DEPTH	31.5 in
PRODUCT HEIGHT	51 in
PRODUCT WIDTH	34.5 in
PRODUCT WEIGHT	1220 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	DOE2016 Efficient
CERTIFICATIONS	UL Listed
CATALOG NOTES	10 CFR Part 431 (2016) Efficient

Physical Attributes	
COIL MATERIAL	Aluminum
ENCLOSURE	NEMA 2
FRAME	FR943
INSULATION	220 °C
MOUNTING	Floor or wall, upright only
TAP SIZE	2 at +2.5%, 4 at -2.5%
TYPE	Energy-efficient ventilated dry-type transformer
WIRING CONNECTION	280B

Miscellaneous	
WEATHERSHIELD	WS60

Performance Ratings	
EFFICIENCY	10 CFR Part 431-2016 (DOE 2016)
FREQUENCY RATING	60 Hz
KVA RATING	150 kVA
PRIMARY VOLTAGE	480 V delta
SECONDARY VOLTAGE	208Y/120 V
SOUND LEVEL	NEMA ST-20
TEMPERATURE RISE	150 °C rise
VOLT AMPERE RATING	150 kVA
VOLTAGE RATING	480 Vac-208Y/120 Vac

Resources	
BROCHURES	Eaton's low-voltage dry-type distribution transformers Eaton's high-efficiency dry-type transformers
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - V48M28T4916

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
 Eaton House
 30 Pembroke Road
 Dublin 4, Ireland
 Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications

Photo is representative

Eaton V48M28T4916

Eaton General purpose ventilated transformer, Fungus proof, AL windings, DOE 2016, NEMA 2, FR943, 220°C, 150 kVA, Fl/wall mt uprt, 3-phase, PV: 480V delta, SV: 208Y/120, NEMA ST-20, 2 at +2.5%, 4 at - 2.5%, 150°C, 150 kVA, WS60, 280B

General specifications

PRODUCT NAME	Eaton General purpose ventilated transformer
CATALOG NUMBER	V48M28T4916
UPC	786680147272
PRODUCT LENGTH/DEPTH	31.5 in
PRODUCT HEIGHT	51 in
PRODUCT WIDTH	34.5 in
PRODUCT WEIGHT	1220 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
COMPLIANCES	DOE2016 Efficient
CERTIFICATIONS	UL Listed
CATALOG NOTES	10 CFR Part 431 (2016) Efficient

Physical Attributes	
COIL MATERIAL	Aluminum
ENCLOSURE	NEMA 2
FRAME	FR943
INSULATION	220 °C
MOUNTING	Floor or wall, upright only
TAP SIZE	2 at +2.5%, 4 at -2.5%
TYPE	Energy-efficient ventilated dry-type transformer
WIRING CONNECTION	280B

Miscellaneous	
WEATHERSHIELD	WS60

Performance Ratings	
EFFICIENCY	10 CFR Part 431-2016 (DOE 2016)
FREQUENCY RATING	60 Hz
KVA RATING	150 kVA
PRIMARY VOLTAGE	480 V delta
SECONDARY VOLTAGE	208Y/120 V
SOUND LEVEL	NEMA ST-20
TEMPERATURE RISE	150 °C rise
VOLT AMPERE RATING	150 kVA
VOLTAGE RATING	480 Vac-208Y/120 Vac

Resources	
BROCHURES	Eaton's low-voltage dry-type distribution transformers Eaton's high-efficiency dry-type transformers
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - V48M28T4916

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
 Eaton House
 30 Pembroke Road
 Dublin 4, Ireland
 Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

