

All Intermatic Weatherproof Covers meet the 2011 NEC current code requirements

Code Requirements:

Intermatic's line of Type 3R receptacle covers ensures compliance with 2011 NEC Article 406.9 (B1) which requires that 15 and 20 ampere, 125 and 250 volt receptacles installed in a wet location have an enclosure that is weatherproof whether or not the attachment plug cap is inserted. They are designed to meet the 2011 NEC Article 210-60(b), which requires that receptacles installed behind beds in hotels and motels, be protected with a suitable guard.


Type 3R

Meets UL and CSA Cold Impact Testing at -60°F (-51°C)

Specifications:


All covers can be used for flush mount, surface mount or FS junction box mounting
 Cover: Clear (gray or white on selected models) UV stabilized polycarbonate
 Mounting Base and Inserts: Black UV stabilized polycarbonate
 Gasket: Neoprene – 1/8" (4.8 mm) thick with slits for mounting screws

These Flexi-Guard Inserts fit single-gang or double-gang models of clear, gray, or white plastic, and extra-duty die-cast designs. Each insert package can be purchased separately. All weatherproof covers come with Flexi-Guard inserts and mounting screws. The double-gang inserts (WP217, WP101, WP102, WP107, and WP213) include a special double-gang gasket.



WP17 Single-Gang Flexi-Guard Inserts

3 standard Flexi-Guard inserts – 16 possible configurations




- Standard in all Flexi-Guard single-gang covers
- 3 separate inserts can be configured into 16 different receptacles or switches
- Converts to either toggle or round receptacle sizes: 1.375", 1.625", 1.75", or 2.125"

WP217


Double-Gang Flexi-Guard Inserts

6 Standard Flexi-Guard inserts – 70 possible configurations




- Can be combined to make the illustrated configurations for double-gang covers

- Converts to either toggle or round receptable sizes: 1.375" or 1.625"




Additional Inserts Available for Flexi-Guard Series:

WP101




Double-Gang Duplex

WP102




Double-Gang GFCI

WP107



Double-Gang Round
1.375", 1.625", 1.75"

WP213



Double-Gang Round
1.375", 1.625", 1.75"

All Intermatic Weatherproof Covers meet the 2011 NEC current code requirements

Code Requirements:

Intermatic's line of Type 3R receptacle covers ensures compliance with 2011 NEC Article 406.9 (B1) which requires that 15 and 20 ampere, 125 and 250 volt receptacles installed in a wet location have an enclosure that is weatherproof whether or not the attachment plug cap is inserted. They are designed to meet the 2011 NEC Article 210-60(b), which requires that receptacles installed behind beds in hotels and motels, be protected with a suitable guard.

Type 3R

Meets UL and CSA Cold Impact Testing at -60°F (-51°C)

Specifications:


All covers can be used for flush mount, surface mount or FS junction box mounting

Cover: Clear (gray or white on selected models) UV stabilized polycarbonate

Mounting Base and Inserts: Black UV stabilized polycarbonate

Gasket: Neoprene – 1/8" (4.8 mm) thick with slits for mounting screws


These Flexi-Guard Inserts fit single-gang or double-gang models of clear, gray, or white plastic, and extra-duty die-cast designs. Each insert package can be purchased separately. All weatherproof covers come with Flexi-Guard inserts and mounting screws. The double-gang inserts (WP217, WP101, WP102, WP107, and WP213) include a special double-gang gasket.



WP17

Single-Gang Flexi-Guard Inserts

3 standard Flexi-Guard inserts – 16 possible configurations




- Standard in all Flexi-Guard single-gang covers
- 3 separate inserts can be configured into 16 different receptacles or switches
- Converts to either toggle or round receptacle sizes: 1.375", 1.625", 1.75", or 2.125"

WP217


Double-Gang Flexi-Guard Inserts

6 Standard Flexi-Guard inserts – 70 possible configurations




- Can be combined to make the illustrated configurations for double-gang covers

- Converts to either toggle or round receptable sizes: 1.375" or 1.625"




Additional Inserts Available for Flexi-Guard Series:

WP101




Double-Gang Duplex

WP102




Double-Gang GFCI

WP107



Double-Gang Round
1.375", 1.625", 1.75"

WP213



Double-Gang Round
1.375", 1.625", 1.75"