

# Specifications



Photo is representative



## Eaton XTOE100DCS

Eaton C440 electronic overload relay, XT IEC Electronic Overload Relay, 20-100A overload range, 55 mm Frame size, NO-NC contact configuration, Direct to contactor mounting, Selectable - 10A, 10, 20, 30 trip type

### General specifications

<b>PRODUCT NAME</b>	Eaton C440 electronic overload relay
<b>CATALOG NUMBER</b>	XTOE100DCS
<b>UPC</b>	786685416557
<b>PRODUCT LENGTH/DEPTH</b>	1.8 in
<b>PRODUCT HEIGHT</b>	4.3 in
<b>PRODUCT WIDTH</b>	1.42 in
<b>PRODUCT WEIGHT</b>	0.87 lb
<b>COMPLIANCES</b>	CE Marked RoHS Compliant ATEX Compliant
<b>CERTIFICATIONS</b>	CSA Certified IEC 60947 EN 60947 UL Listed



Powering Business Worldwide

## Product specifications

OVERLOAD RANGE	20-100A
TYPE	Electronic overload relay
FRAME SIZE	55 mm
MOUNTING METHOD	Direct
CONTACT CONFIGURATION	NO, NC
TRIP TYPE	Selectable 10 A, class 10 ,20, 30

## Resources

BROCHURES	<a href="#">C440 Electronic Overload Relay</a>
CATALOGS	<a href="#">Motor Control and Protection, NEMA Contactors and Starters, Volume 5, Tab 2</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - XTOE100DCS</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



# Specifications



Photo is representative



## Eaton XTOE100DCS

Eaton C440 electronic overload relay, XT IEC Electronic Overload Relay, 20-100A overload range, 55 mm Frame size, NO-NC contact configuration, Direct to contactor mounting, Selectable - 10A, 10, 20, 30 trip type

### General specifications

<b>PRODUCT NAME</b>	Eaton C440 electronic overload relay
<b>CATALOG NUMBER</b>	XTOE100DCS
<b>UPC</b>	786685416557
<b>PRODUCT LENGTH/DEPTH</b>	1.8 in
<b>PRODUCT HEIGHT</b>	4.3 in
<b>PRODUCT WIDTH</b>	1.42 in
<b>PRODUCT WEIGHT</b>	0.87 lb
<b>COMPLIANCES</b>	CE Marked RoHS Compliant ATEX Compliant
<b>CERTIFICATIONS</b>	CSA Certified IEC 60947 EN 60947 UL Listed



Powering Business Worldwide

## Product specifications

OVERLOAD RANGE	20-100A
TYPE	Electronic overload relay
FRAME SIZE	55 mm
MOUNTING METHOD	Direct
CONTACT CONFIGURATION	NO, NC
TRIP TYPE	Selectable 10 A, class 10 ,20, 30

## Resources

BROCHURES	<a href="#">C440 Electronic Overload Relay</a>
CATALOGS	<a href="#">Motor Control and Protection, NEMA Contactors and Starters, Volume 5, Tab 2</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - XTOE100DCS</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

